

Description: Ferro Corporation offers a full range of thick film inks for contacting the back surface of silicon solar cells. The most common class of materials for bus bar and grid applications is an aluminum-doped silver formulation. The purpose of the aluminum is to reduce the ohmic contact resistance between the thick film material and the p-doped silicon surface. The other classes of back surface metallizations offered are pure aluminum inks. These inks, which come in fritted and unfritted versions, are used to form a p+ back surface field layer. A variety of configurations and process sequences can be accommodated by combinations of our product offerings.

5540 is a pure aluminum paste designed for application to the backside of mono- and polycrystalline silicon solar cells. The product displays very low contact resistance and is compatible with several Ferro silver and silver/aluminum conductors.

Processing Recommendations

Printing: 200 – 325 mesh screen with a 20 μm – 25 μm emulsion thickness is recommended.

Drying: The ink can be dried in an Infrared or conventional dryer under wide range of conditions. Inks are typically dried in a IR dryer with set points of 250°C – 300°C in less than 20 seconds.

Thinning: Thinning is not recommended, since the paste is supplied at the correct viscosity for application. Contact your local Ferro Representative for appropriate solvent details, should thinning become necessary to replace solvent lost through evaporation.

Paste Storage & Shelf Life: The paste should be stored in tightly capped containers, in a cool, dry place away from direct sunlight. Properly stored material will have a shelf life in excess of 6 months.

Typical Properties	
	5540
Viscosity (poise) ¹ :	500 – 700
Fineness of Grind:	< 37 μm
Dried Thickness:	30 – 40 μm
Fired Thickness:	25 – 35 μm
Wet Deposit (grams/square inch):	0.065
Drying Profile:	250 – 300°C, < 20 seconds
Peak Firing Temp:	680 – 750°C
Time at Peak:	1 – 20 seconds
Recommended Thinner	0804

Notes:

¹Viscosity as measured on Brookfield model HBT cone/plate viscometer; 9.6 reciprocal seconds, 1.565"cone, 25°C.

Rev: 09/05

www.ferro.com

DISCLAIMER: Reasonable care has been taken in the preparation of this information, but **FERRO EXTENDS NO WARRANTIES, MAKES NO REPRESENTATIONS AND ASSUMES NO RESPONSIBILITY AS TO ACCURACY OR SUITABILITY OF THIS INFORMATION OF THIS PRODUCT FOR ANY PURCHASER'S OR USER'S USE OR FOR ANY CONSEQUENCE OF ITS USE. FERRO DISCLAIMS ANY WARRANTY OF MERCHANTABILITY OR WARRANTY OF FITNESS FOR ANY PARTICULAR USE.** All statements, technical information and recommendations contained herein are based on Seller's or Manufacturer's test and the test of others, and are believed to be accurate, but no guarantee of accuracy is made. Judgment as to the suitability of information herein or the user's purposes are necessarily the user's responsibility. Users shall determine the suitability of the products for their own intended application.

Users assume all risk of use or handling whether or not in accordance with any statements or recommendation of the seller or manufacturer. Liability, if any, is and shall be limited to the replacement of such quantity of material proved not to conform to specifications as set out in product specification. Statements concerning the possible use of these products are not intended as recommendation to use these products in infringement of any patent. No guarantee is made that any use of the products does not infringe third-party intellectual property or patent rights anywhere in the world.